



Quality Products. Service Excellence.

Formed Steel Rack Panels *PBFS Series*

Also referred to as a Spacer Blank Panel

Features



- Constructed of 16-gauge steel.
- Fits standard 19in EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder coat. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America.



Accessories

- Hardware for Rack Mounting Solutions
- Rack Rail Reducer Panel



RAL9005 Matte Black Part No.	ANSI61 Dark Gray Part No.	RAL7035 Light Gray Part No.	RAL9003 Matt White Part No.	Panel Height		Qty of Mounting Points
				Rack Units	Panel Height	
PBFS19000BK	-	-	-	1/2U	0.09	2
PBFS19001BK	PBFS19001GY2	PBFS19001LG2	PBFS19001WH	1U	1.75	4
PBFS19003BK	PBFS19003GY2	PBFS19003LG2	PBFS19003WH	2U	3.50	4
PBFS19005BK	PBFS19005GY2	PBFS19005LG2	PBFS19005WH	3U	5.25	4
PBFS19007BK	PBFS19007GY2	PBFS19007LG2	PBFS19007WH	4U	7.00	4
PBFS19008BK	PBFS19008GY2	PBFS19008LG2	PBFS19008WH	5U	8.75	4
PBFS19010BK	PBFS19010GY2	PBFS19010LG2	PBFS19010WH	6U	10.50	8
PBFS19012BK	PBFS19012GY2	PBFS19012LG2	PBFS19012WH	7U	12.25	8
PBFS19014BK	PBFS19014GY2	PBFS19014LG2	PBFS19014WH	8U	14.00	8
PBFS19015BK	PBFS19015GY2	PBFS19015LG2	PBFS19015WH	9U	15.75	8
PBFS19017BK	PBFS19017GY2	PBFS19017LG2	PBFS19017WH	10U	17.50	8

Tags: Flanged, Folded

Data subject to change without notice

