



1.2x1.0mm Ceramic SMD Crystal CABS

DATASHEET

- Tolerances down to ± 10 PPM
- Stabilities down to ± 10 PPM
- Temperature Ranges as wide as -40°C to $+85^{\circ}\text{C}$

• SPECIFICATIONS


PARAMETERS	MAX (unless otherwise noted)
Frequency Range	32.000 ~ 80.000 MHz
Frequency Tolerance @ 25°C	(See options on page 2)
Frequency Stability, ref @ 25°C	(See options below)
Temperature Range	
Operating (TOPR)	(See options below)
Storage (TSTG)	-55°C ~ $+125^{\circ}\text{C}$
Shunt Capacitance (Co)	2 pF
Load Capacitance (CL)	(See options on page 2)
Drive Level	100 μW (10 μW typical)
Aging per year	± 3 PPM
Maximum Soldering Temp / Time	260 $^{\circ}\text{C}$ / 10 Seconds x 2
Moisture Sensitivity Level (MSL) per J-STD-033	N/A
Termination Finish	Au (0.3~1 μm) over Ni (1.27~8.89 μm)
Lead (Pb) Free	Yes
RoHS Compliant	Yes, no exemptions
REACH Compliant (latest version)	Yes

Frequency Range (MHz)	Operating Mode	Max ESR Ω
32.000 ~ 32.999999	Fundamental	100
33.000 ~ 36.999999	Fundamental	80
37.000 ~ 80.000	Fundamental	60

• Available Operating Temperatures and Stabilities

Operating Temperature	± 10 PPM	± 15 PPM	± 20 PPM	± 25 PPM
-20 ~ $+70^{\circ}\text{C}$	O	O	O	O
-30 ~ $+85^{\circ}\text{C}$	X	O	O	O
-40 ~ $+85^{\circ}\text{C}$	X	O	O	O

Key: O=Available, X=Not Available



Note: Dimensional drawing is for reference to critical specifications defined by size measurements. Certain non-critical visual attributes, such as side castellations, etc. may vary.



1.2x1.0mm Ceramic SMD Crystal CABS

DATASHEET

• TAPE SPECIFICATIONS (millimeters)							• REEL SPECIFICATIONS (millimeters)						
A	B	C	D	E	F	Reel QTY	G	H	I	J	K	L	M
Ø1.5	4.0	4.0	3.5	8.0	0.45	-T5 = 5,000	2.0	Ø13	Ø21	Ø60	Ø180	9.0	1.5
Direction of Pull													

Available Options & Part Identification for CABS¹

F CABS F F D M 40.0

F	CABS	F	F	D	M	40.0
FOX	Model Number	Tolerance D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	Stability D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	Load Capacitance² B = 6 pF V = 7 pF D = 8 pF E = 10 pF G = 12 pF	Operating Temperature F = -20 ~ +70°C K = -30 ~ +85°C M = -40 ~ +85°C	Frequency (MHz)

¹Not all frequency, tolerance, stability, load, and operating temperature combinations may be available.

²Listed load capacitances represent the most commonly used. Other load capacitances are available.



Corporate Headquarters

5570 Enterprise Parkway
Fort Myers, FL 33905
<http://www.FOXONLINE.com>

Sales

1-888-GET-2-FOX (1-888-438-2369) or
1-239-693-0099
<http://www.FOXONLINE.com/repdisty>

Tech Support

<http://www.FOXONLINE.com/email>

PRODUCT USE: Fox Electronics reserves the right to modify the products and/or specifications described herein at any time and at Fox Electronics' sole discretion. All information in this document, including descriptions of product features and performance, is subject to change without notice. Performance specifications and the operating parameters of the described products are determined in the independent state and are not guaranteed to perform the same way when installed in customer products. The information contained herein is provided without representation or warranty of any kind, whether express or implied, including, but not limited to, the suitability of Fox Electronics' products for any particular purpose, an implied warranty of merchantability, or non-infringement of the intellectual property rights of others. This document is presented only as a guide and does not convey any license under intellectual property rights of Fox Electronics or any third parties.

Fox Electronics' products are not intended for use in applications involving extreme environmental conditions or in life support systems or similar devices where the failure or malfunction of a Fox Electronics product can be reasonably expected to significantly affect the health or safety of users. Anyone using a Fox Electronics product in such a manner does so at their own risk, absent an express, written agreement by Fox Electronics.

Fox Electronics and the Fox logo are registered trademarks of Fox Electronics. Product specification is subject to change without notice. Other trademarks and service marks used herein, including protected names, logos and designs, are the property of Fox Electronics or their respective third-party owners.

For datasheet type definitions and a glossary of common terms, visit <http://www.foxonline.com/tgcristals.html>.

7/23/2020 - Added thickness info to termination metals, adjusted MSL info to include J-STD-033 and N/A.

Title / Description: CABS SERIES STANDARD SPECIFICATIONS

Drawing Number: CABS-DOC-1

Size: A

Part Number:

Cage: 61429

Draftsperson: BEC

Approved: MAJ

Revision Date: 07/23/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fox:

[FCABSFEVK38.4](#) [FCABSFEVK37.4](#) [FCABSFEVK52.0](#)